



OLIVIA™ C130 ROLLING MILL

SKU: 1035

The new Olivia™ C130 Rolling Mill, Unique Patent pending 50-1 Gearbox. This revolutionary design makes rolling so much easier. The new easy glide gearbox allows for an even wider range of people to operate a rolling mill with ease.

Standing or sitting, this rolling mill is a joy to use for all abilities and of course still offers all the quality you would expect from Durston.

UK Patent Pending # 2010974.0 International Patent Pending # PCT/EP2021/068551

Olivia ™ C130 Combination Rolling Mill

- Operated with ease standing or sitting using the front turning wheel
- 50-to-1 reduction gearbox
- Side extension with 4 half round grooves (4 to 1.5mm)
- 11 Square wire rolling grooves (Main Roll)
- Flat rolling area 75mm (Main Roll)
- Roll diameter 60mm
- Roll width 130mm (75mm / 55mm)
- Full description below

The first 1000 Olivia 130 Rolling Mills sold will all come with a signed original picture of Olivia Durston.

PRODUCT DESCRIPTION

As with all of our Rolling Mills the Olivia™ features a solid single cast body, induction hardened rolls and our



classic highly calibrated adjustment wheel ensuring a lifetime of rolling with professional results.

The 50-1 gearbox, making it that much easier to Roll out material, will take 50 turns of the handwheel to turn the rolls once. The gearbox and handwheel have been designed to work together to make turning so much easier. The specially designed Patent Pending gearbox along with the inertia of the handwheel means you can turn the handwheel up to 10 times as quick as a standard rolling mill with a 4-1 reduction

The Olivia™ C130 is a Combination Rolling Mill designed for flat metals, wire and and half round wire (using the side extension). Durston Rolling Mills are proven to be solid, reliable workhorses in many jewellers' workshops and factories offering years of service. The Olivia™ C130 is no exception.

What's special about Olivia™?

- Apart from the obvious 50-1 gearbox making it that much easier to roll out material.
- Now you can sit down using a Rolling Mill. or stand up. Whatever you prefer.
- Great for people with bad backs, disabilities, or those who find it difficult to move around or stand up for long periods.
- Great for shorter people or for those who find long reach arm movement difficult.
- Increased productivity. Now you can move from the bench to Rolling Mill without standing up and moving across the room.
- More compact. All one unit without the need for additional turning space.
- Now you can place your Rolling Mill anywhere along the bench to suit you. No need to place it at the end.
- Smoother operation for a better-rolled product.
- Great for Roller printing as more tension can be applied.
- It's not just a Durston. Its an "Olivia Durston"

Additional Resources:

Additional or Replacement Extension Rollers available for this model:

Extension Roller 8, 6 & 3mm for Olivia 130

Extension Roller 10 & 7mm for Olivia 130

Extension Roller 4, 3, 2 & 1.5mm for Olivia 130 (Included as standard)

Extension Roller Plain for Olivia 130 (Included as standard)

Click here to download the mounting hole diagram.

Click here to download the product diagram with dimensions.

Please read our Rolling Mill FAQs tab for more information.

The Olivia™ Story... Read More..



WHERE IT ALL BEGAN...

Founder, William Durston (left) early 1970s also, Williams Dad Christopher Durston machining parts for rolling mills.

View Durston History

ADDITIONAL INFORMATION

Weight 67.5 kg

Dimensions $60 \times 47 \times 54 \text{ cm}$

Product Length (mm) 220

Product Width (mm) 490

Product Height (mm) 540

Gearbox 50-to-1 gearbox

Max. Sheet Thickness (mm) 6mm

Roller Type <u>Combination</u>

Roller diameter (mm) 60

Roller Length (mm) 130

Side Extensions 4, 3, 2, 1.5mm